



## Core LED torch with rechargeable battery, Type: P2R-CORE



### Order data

Order number	081468 P2R-CORE
GTIN	4058205020367
Item class	04B

### Description

#### Version:

LED lenses are amongst the technology leaders for LED torches. Within the **splash-proof aluminium housing**, all the contacts are gold-plated, **high-quality lenses** gather the light uniformly and without losses. All lamps are equipped with focussable lamp head.

Core series Ledlenser, the new generation of the well-known P series.

#### Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

#### Supplied with:

Supplied with USB charging cable.

### Technical description

Type of rechargeable battery	Lithium-ion
Illumination time	0.5 h
Overall length	103 mm
Illumination step 3	15 lm
Illumination	120 lm
IP Index of Protection	IP 54
Weight	36 g
Illumination time stage 3	5 h

Illumination step 2	50 lm
Illumination time stage 2	1 h
Head Ø	15 mm
Number of rechargeable batteries contained	1
Power supply	Rechargeable battery-powered
Type of product	Flashlight