



## Core LED torch with rechargeable battery, Type: P7R-CORE



### Order data

Order number	081468 P7R-CORE
GTIN	4058205020510
Item class	04B

### Description

#### Version:

LED lenses are amongst the technology leaders for LED torches. Within the **splash-proof aluminium housing**, all the contacts are gold-plated, **high-quality lenses** gather the light uniformly and without losses. All lamps are equipped with focussable lamp head.

Core series Ledlenser, the new generation of the well-known P series.

#### Function:

IP68: Protected against continuous submersion in water (watertight) and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

Supplied with USB charging cable and wrist strap.

### Technical description

Illumination time stage 3	90 h
Weight	202 g
Illumination step 3	15 lm
Illumination step 2	440 lm
Head Ø	35 mm
Illumination time stage 2	4 h
Power supply	Rechargeable battery-powered
Illumination	1000 lm

Type of rechargeable battery	Lithium-ion
Illumination time	2 h
Overall length	158 mm
Number of rechargeable batteries contained	1
IP Index of Protection	IP 68
Type of product	Flashlight