



LED headlamp with rechargeable battery, Type: H5R-CORE



Order data

Order number	081479 H5R-CORE
GTIN	4058205020879
Item class	04B

Description

Version:

Powerful high-performance LED headlamps for professional use.

- **Pivoting head and stepless focussing function.**
- **Intuitive operation and stepless dimming.**
- **Exchangeable and washable head band.**
- **Ledlenser connecting system as a standardised interface permits easy connection with a comprehensive range of accessories.**

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Technical description

Light current boost	500 lm
IP Index of Protection	IP 67
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Illumination time	2 h
Head Ø	32 mm
Illumination time stage 2	50 h
Illumination	400 lm

Number of rechargeable batteries contained	1
Manufacturer's designation	H5R Core
Weight	167 g
Illumination step 2	15 lm
Type of product	Headlamp