



## Boring bar holder Form E2, VDI 16, Bore d<sub>2</sub> (H7): 16mm



### Order data

Order number	319305 16
GTIN	4062406745905
Item class	32U

### Description

#### Version:

- Case-hardened HRC 58+/-2.
- All functional faces ground.
- Through-bored VDI shank.
- With two ball spray nozzles.

#### Advantage:

- Also suitable for longer boring bars.
- Individual length adjustment for the boring bars.

#### Application:

For internal machining with boring bar holder.

#### Standard:

DIN 69880 / VDI 3425, Blatt 2.

### Technical description

Bore d <sub>2</sub> (H7)	16 mm
l <sub>7</sub>	34 mm
l <sub>6</sub>	44 mm
Cooling channel thread	M5
Clamping screw thread	M8

Shape	E
VDI size	VDI 16
d <sub>6</sub>	40 mm
Colour code for VDI shanks	VDI 16
Type of product	VDI boring bar toolholder