

**Boring bar holder Form E2, VDI 16, Bore d2 (H7): 12mm****Order data**

Order number	319305 12
GTIN	4062406745899
Item class	32U

**Description****Version:**

- **Case-hardened HRC 58+/-2.**
- **All functional faces ground.**
- **Through-bored VDI shank.**
- **With two ball spray nozzles.**

**Advantage:**

- **Also suitable for longer boring bars.**
- **Individual length adjustment for the boring bars.**

**Application:**

For internal machining with boring bar holder.

**Standard:**

**DIN 69880 / VDI 3425, Blatt 2.**

**Technical description**

$l_6$	44 mm
$l_7$	34 mm
Bore d <sub>2</sub> (H7)	12 mm
Cooling channel thread	M5
Clamping screw thread	M8

Shape	E
VDI size	VDI 16
d <sub>6</sub>	40 mm
Colour code for VDI shanks	VDI 16
Type of product	VDI boring bar toolholder