



Indexable drill holder Form E1, VDI 20, Bore d₂ (H6): 20mm



Order data

Order number	319155 20
GTIN	4062406755164
Item class	32U

Description

Application:

For drilling with indexable drill with internal coolant supply.

Standard:

DIN 69880 / VDI 3425, Blatt 2.

Technical description

Bore d ₂ (H6)	20 mm
l ₁ -0.2	67 mm
External Ø d ₃	40 mm
l ₂	54 mm
Cooling channel thread	M6
Clamping screw thread	M10×1
Shape	E
VDI size	VDI 20
d ₆	50 mm
Colour code for VDI shanks	VDI 20

Type of product

VDI tool arbor