



Indexable drill holder Form E1, VDI 25, Bore d₂ (H6): 25mm



Order data

Order number	319165 25
GTIN	4062406755201
Item class	32U

Description

Application:

For drilling with indexable drill with internal coolant supply.

Standard:

DIN 69880 / VDI 3425, Blatt 2.

Technical description

l ₂	59 mm
External Ø d ₃	45 mm
Bore d ₂ (H6)	25 mm
l ₁ -0.2	75 mm
Cooling channel thread	M8
Clamping screw thread	M12×1
Shape	E
VDI size	VDI 25
d ₆	58 mm
Colour code for VDI shanks	VDI 25

Type of product

VDI tool arbor