



Indexable drill holder Form E1, VDI 40, Bore d₂ (H6): 40mm



Order data

Order number	319205 40
GTIN	4062406755300
Item class	32U

Description

Application:

For drilling with indexable drill with internal coolant supply.

Standard:

DIN 69880 / VDI 3425, Blatt 2.

Technical description

Bore d ₂ (H6)	40 mm
External Ø d ₃	65 mm
l ₂	73 mm
l ₁ -0.2	90 mm
Cooling channel thread	M8
Clamping screw thread	M16×1
Shape	E
VDI size	VDI 40
d ₆	83 mm
Colour code for VDI shanks	VDI 40

Type of product

VDI tool arbor