

Garant

**Workstation with electric height adjustment Load capacity max. 250 / 200 kg
dark Eluplan worktop, Type: 1250**

**Order data**

Order number	920301 1250
GTIN	4062406755362
Item class	9GG

Description**Version:**

Base frame with lift unit with cross braces for stabilisation at the side and rear. 50 mm thick worktop made of dark Eluplan. Work bench **without** side plates, not suitable for installing in a row.

Colour:

Height-adjustable feet in black, cross braces in RAL 7016 anthracite **powder-coated**.

Recommendation:

Light assembly work, sitting and standing.

Note:

Because of the maximum load capacity, only mobile casings should be used. Avoid attaching casings under the worktop. Further attachments would reduce the load capacity correspondingly. Delivered fully assembled.

Technical description

Width	1250 mm
Nominal voltage	250 V
Height adjustment range (worktop surface) from – to	610 - 1200 mm

maximum load capacity	250 kg
Plug type, input	F
Material of worktop	Eluplan, dark
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Weight	94 kg
Lifting speed	38 mm/s
Depth	750 mm
Continuous load capacity	250 kg
Worktop length	1250 mm
Worktop depth	750 mm
ComfortClose	no
Control panel with display and memory functions	yes
Worktop thickness	50 mm
Material thickness	1 mm
Type of height adjustment	electrical
Insert thickness	50 mm
Type of product	Work table