

Garant GRIDLINE

**Support leg with power and compressed air, Height 800 mm, Type: CH****Order data**

Order number	927067 CH
GTIN	4062406755621
Item class	9GG

**Description****Version:**

Of steel hollow section, 50 mm wide with cross bracing and mounting for height adjustment at 25 mm intervals. Feet with plastic pads, do not damage the floor. With cable slots - for simple and professional routing of media cables / power cables.

**Supplied with:**

Support leg with two Schuko sockets with fastening materials, not wired.

Incl. safety one-hand coupling, quick-release coupling nominal value 7.2 and 3/8 inch connection thread, up to 10 bar.

**Colour:**

RAL 7035 light grey **powder-coated**.

**Note:**

Support legs without rear panel or cupboards require stabilising plates No. 927122 for stiffening. The height is to the underside of the worktop.

Pre-assembled workbenches must be secured against tipping.

**Technical description**

Height	800 mm
Nominal voltage	250 V

suitable for worktop depth	750 mm
Socket type	J
Rated current	10 A
Depth	700 mm
Width	50 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	Height 800 mm
Type of product	Power module

---

## Accessories

Height adjustment for GridLine workbenches Type M12	927090 M12
Floor pads, set, 2 pieces Type 2	927092 2