

Garant GRIDLINE

Support leg with power and compressed air, Height 900 mm, Type: FR**Order data**

Order number	927068 FR
GTIN	4062406755683
Item class	9GG

Description**Version:**

Of steel hollow section, 50 mm wide with cross bracing and mounting for height adjustment at 25 mm intervals. Feet with plastic pads, do not damage the floor. With cable slots - for simple and professional routing of media cables / power cables.

Supplied with:

Support leg with two Schuko sockets with fastening materials, not wired.

Incl. safety one-hand coupling, quick-release coupling nominal value 7.2 and 3/8 inch connection thread, up to 10 bar.

Colour:

RAL 7035 light grey **powder-coated**.

Note:

Support legs without rear panel or cupboards require stabilising plates No. 927122 for stiffening. The height is to the underside of the worktop.

Pre-assembled workbenches must be secured against tipping.

Technical description

Nominal voltage	250 V
Socket type	E

Rated current	16 A
Height	900 mm
Depth	700 mm
suitable for worktop depth	750 mm
Width	50 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	Height 900 mm
Type of product	Power module

Accessories

Height adjustment for GridLine workbenches Type M12	927090 M12
Floor pads, set, 2 pieces Type 2	927092 2