

Garant GRIDLINE

Support leg with power and compressed air, Height 900 mm, Type: CZ**Order data**

| | |
|--------------|---------------|
| Order number | 927068 CZ |
| GTIN | 4062406755706 |
| Item class | 9GG |

Description**Version:**

Of steel hollow section, 50 mm wide with cross bracing and mounting for height adjustment at 25 mm intervals. Feet with plastic pads, do not damage the floor. With cable slots - for simple and professional routing of media cables / power cables.

Supplied with:

Support leg with two Schuko sockets with fastening materials, not wired.

Incl. safety one-hand coupling, quick-release coupling nominal value 7.2 and 3/8 inch connection thread, up to 10 bar.

Colour:

RAL 7035 light grey **powder-coated**.

Note:

Support legs without rear panel or cupboards require stabilising plates No. 927122 for stiffening. The height is to the underside of the worktop.

Pre-assembled workbenches must be secured against tipping.

Technical description

| | |
|-----------------|-------|
| Nominal voltage | 250 V |
| Width | 50 mm |

| | |
|----------------------------|---|
| Socket type | E |
| suitable for worktop depth | 750 mm |
| Rated current | 16 A |
| Depth | 700 mm |
| Height | 900 mm |
| Design version | Steel hollow section construction |
| Material thickness | 1 mm |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Product name attribute | Height 900 mm |
| Type of product | Power module |

Accessories

| | |
|---|------------|
| Height adjustment for GridLine workbenches Type M12 | 927090 M12 |
| Floor pads, set, 2 pieces Type 2 | 927092 2 |