

Garant GRIDLINE

Support leg with power, Height 900 mm, Type: CH**Order data**

Order number	927063 CH
GTIN	4062406755577
Item class	9GG

Description**Version:**

Of steel hollow section, 50 mm wide with cross bracing and mounting for height adjustment at 25 mm intervals. Feet with plastic pads, do not damage the floor. With cable slots - for simple and professional routing of media cables / power cables.

Supplied with:

Support leg with two Schuko sockets with fastening materials, not wired.

Colour:

RAL 7035 light grey **powder-coated**.

Note:

Support legs without rear panel or cupboards require stabilising plates No. 927122 for stiffening. The height is to the underside of the worktop.

Pre-assembled workbenches must be secured against tipping.

Technical description

suitable for worktop depth	750 mm
Height	800 mm
Depth	700 mm

Nominal voltage	250 V
Socket type	J
Rated current	10 A
Width	50 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	Height 900 mm
Type of product	Power module

Accessories

Height adjustment for GridLine workbenches Type M12	927090 M12
-----------------------------------------------------	------------