



LED headlamp with battery, Type: H5-CORE



Order data

Order number	081390 H5-CORE
GTIN	4058205020848
Item class	04B

Description

Version:

Powerful high-performance LED headlamps for professional use.

- **Pivoting head and stepless focussing function.**
- **Intuitive operation and stepless dimming.**
- **Exchangeable and washable head band.**
- **Ledlenser connecting system as a standardised interface permits easy connection with a comprehensive range of accessories.**

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Technical description

Weight	178 g
IP Index of Protection	IP 67
Illumination time	2 h
Illumination time stage 2	20 h
Head Ø	32 mm
Illumination step 2	15 lm
Illumination	200 lm
Power supply	Battery-powered

Manufacturer's designation	H5 Core
Battery type	Mignon, AA
Number of batteries contained	2
Light current boost	350 lm
Type of product	Headlamp