



TMSERROR, Type: LITHIUM4



Order data

Order number	081590 LITHIUM4
GTIN	4013674183562
Item class	08C

Description

Version:

Microprocessor-controlled charging and servicing stations for battery cells with **individual channel monitoring** and battery fault detection. Status display for each charging slot, automatic charging switch-off, overload protection and **trickle charging**. Input voltage 100–240 V. With LC display for detailed monitoring of the charging process and additional acoustic feedback.

Application:

NiMH battery charging points: 1 – 4 × Micro AAA / Mignon AA or 1 – 2 × Baby C. **Li-ion /**

LiFePO4 battery charging points: 1 – 4 × 18650; 17670; 14500 etc.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB

Technical description

Maximum number of charging points	4
Width	96 mm
Height	33 mm
Nominal voltage	100 V
maximum charging current	2 A
suitable battery - supplier / battery type / voltage	Type CAS 18 V

Length	129.5 mm
Mains frequency	50 Hz
Interface	Digimatic interface
Type of product	Battery charger