

**KERN**
**Counting scales, type CIB, maximum weighing range: 3kg**

**Order data**

Order number	479541 3
GTIN	4045761214880
Item class	47D

**Description**
**Version:**

- **Precision counting scales with automatic reference optimisation (refines the average piece weight value in stages).**
- **Target quantity and target weight programmable to give an acoustic signal.**
- **Cumulative quantity memory for totalling weighings of identical parts by total quantity and total weight.**
- **Selectable reference piece numbers or reference weight.**
- **Selectable mains and battery operation.**
- **Adjustment programme CAL: For accuracy adjustment (external calibration weight available on request if required).**
- **Display selectable between pieces and weight.**

Checkweighing display: Acoustic or visual feedback if weighing is outside a pre-determined limit value.

**Supplied with:**

Mains adapter 230 V / 50 Hz, battery and protective hood.

**Technical description**

Height	120 mm
Power supply	Rechargeable battery-powered
Power supply	Mains-powered

Nominal voltage	240 V
Minimum unit weight	1 g
Depth	330 mm
Net weight	3.5 kg
Width	350 mm
Settling time	2 s
Dimensions of weighing plate	315×215 mm
maximum weighing range	3 kg
Scale divisions	0.2 g
Reproducibility	0.2 g
Linearity	±0.4 g
Calibration	K2
Type of product	Counting balance

## Services

DAkkS calibrationScales maximum weighing range 50	027710 50
CalibrationScales maximum weighing range 50 kg	027700 50