

HEDI

All-plastic cable drum, Type: 25N



Order data

Order number	081103 25N
GTIN	4003644024179
Item class	08B

Description

Version:

HEDI® cable drums stand for "Made in Germany" quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental rotation of the drum. All cable drums are equipped with thermal cut-out switches.

Compact, high-quality HEDI® all-plastic cable reels with a reel diameter of 250 mm and ergonomic and safety features.

- **Inclined 7 degrees for greater ground clearance and to make it comfortable to carry.**
- **Removable cable holder and guide for optimum cable control.**
- **Easy to mount on a wall.**

Certified for continuous exterior use and for use in humid environments.

Function:

IP44: Protected against splashed water from all directions and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

Technical description

IP Index of Protection	IP 44
------------------------	-------

Number of sockets	3
Cable structure	3G1.5
Rated power unrolled	3500 (16 A) W
Material cable	Neoprene rubber
impact-resistant and splash-proof	Category 2 (K2) to BGI
Nominal voltage	250 V
Power supply	Mains-powered
Diagnostic system present	yes
Cable class	H07RN-F
Cable length	25 m
Material of body	Plastic
Type of product	Cable drum