

HEDI**All-plastic cable drum for F, B, PL, CZ, Type: 50N****Order data**

Order number	081104 50N
GTIN	4003644024117
Item class	08B

Description**Version:**

HEDI® cable drums stand for "Made in Germany" quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental rotation of the drum. All cable drums are equipped with thermal cut-out switches.

Compact, high-quality HEDI® all-plastic cable reels with a reel diameter of 250 mm and ergonomic and safety features.

- **Inclined 7 degrees for greater ground clearance and to make it comfortable to carry.**
- **Removable cable holder and guide for optimum cable control.**
- **Easy to mount on a wall.**

Certified for continuous exterior use and for use in humid environments.

Function:

IP44: Protected against splashed water from all directions and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

IP Index of Protection: IP 44

impact-resistant and splash-proof: Category 2 (K2) to BGI

Rated power unrolled: 3500 (16A) W

Cable class: H07RN-F

Cable structure: 3G1.5

Material cable: Rubber

Cable length: 50 m
Number of sockets: 3

Technical description

Material of body	Plastic
Rated power unrolled	3500 (16A) W
Cable class	H07RN-F
Cable length	50 m
Number of sockets	3
IP Index of Protection	IP 44
Nominal voltage	250 V
impact-resistant and splash-proof	Category 2 (K2) to BGI
Cable structure	3G1.5
Material cable	Rubber
Diagnostic system present	yes
Type of product	Cable drum