

Garant GRIDLINE

Tool cabinet complete with drawers 75 kg, 20×24G, Height mm / number of drawers: 900/6**Order data**

Order number	931005 900/6
GTIN	4062406769277
Item class	9GK

Description**Version:**

Completely equipped tool cabinet in 24×28G, with drawers 20×24G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Technical description

Depth	700 mm
Drawer usable width	500 mm
Number of drawers	6

Drawer front height	75 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	125 mm
Drawer front height	150 mm
Drawer front height	250 mm
Drawer usable width in G	20
Width	600 mm
Usable height	800 mm
Height	900 mm
Usable height for drawers	800 mm
Drawer usable depth	600 mm
Drawer usable area in G	20×24
Weight	109 kg
Drawer usable depth in G	24
Number of doors	0
Number of pull-out shelves	0
Base cabinet underneath height-adjustable workstation	no
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×24G
Type of product	Tool cabinet

Accessories

Tool cabinet casing for drawers Height 900 mm	931035 900
Drawer,75 kg Drawer front height 100 mm	931043 100
Drawer,75 kg Drawer front height 125 mm	931043 125
Drawer,75 kg Drawer front height 150 mm	931043 150
Drawer,75 kg Drawer front height 250 mm	931043 250
Drawer,75 kg Drawer front height 75 mm	931043 75
Lock plate for GridLine Type HU21	914227 HU21