

Garant**DC.T 070202, Grade: HB7315-1**

Order data

Order number	260351 HB7315-1
GTIN	4062406769857
Item class	21G

Description

DCMT 070202 HB7315-1 Grade: HB7315-1
Chip breaker: AF
Tolerance: G
Cutting depth a_p : 0.05 - 0.6 mm
Feed f : 0.03 - 0.1 mm/rev.
Cutting speed v_c main application: 120 - 600 m/min

Technical description

Main application	N
Tolerance	G
ISO code indexable insert	DCGT 070202
Chip breaker	AF
Number of changes/inserts	2
Tool material	Carbide

Corner radius	0.2 mm
Grade	HB7315-1
Feed f	0.03 - 0.1 mm/rev.
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.05 - 0.6 mm
Cutting speed v_c main application	120 - 600 m/min
Cutting conditions	continuous
Type of product	Indexable insert for turning