

**JEPSON** POWER**Drytech® circular saw blade Ø 203 mm, Number of teeth: 54****Order data**

Order number	078243 54
GTIN	4260052468104
Item class	07E

**Description****Version:**

Ideal for sawing metal grids and racks, trapezoidal sheets, profiles, cable ducts, roller shutter tubes, etc. At 1.0 to 1.7 mm, the LBS saw blades are much thinner than conventional saw blades. This means they save material and are more efficient and quicker. Energy-saving, resulting in more battery power. Cutting speed max. 4000 rpm.

**Technical description**

Suitable for materials	INOX
Width of cut B	1.7 mm
Number of teeth	54
Bore Ø	25.4 mm
Blade Ø D	203 mm
Type of product	Circular saw blade

