

JEPSON POWER**Drytech® circular saw blade Ø 203 mm, Number of teeth: 48****Order data**

Order number	078243 48
GTIN	4260052466780
Item class	07E

Description**Version:**

Ideal for sawing metal grids and racks, trapezoidal sheets, profiles, cable ducts, roller shutter tubes, etc. At 1.0 to 1.7 mm, the LBS saw blades are much thinner than conventional saw blades. This means they save material and are more efficient and quicker. Energy-saving, resulting in more battery power. Cutting speed max. 3800 rpm.

Technical description

Blade Ø D	203 mm
Number of teeth	48
Suitable for materials	Steel
Width of cut B	1.2 mm
Bore Ø	25.4 mm
Type of product	Circular saw blade

