

Garant
Carbide masonry drill, Drill Ø: 7mm

Order data

Order number	786070 7
GTIN	4062406773427
Item class	71C

Description
Version:

Drill tipped with hard and tough carbide inserts and brazed at high temperature. Asymmetrical flute profile for good transport of drill dust.

Hammer and rotary bits with strong carbide cutter tip.

Application:

Primarily for **drilling dowel holes with hammer drills** in concrete, masonry, natural and synthetic stone.

Also for rotary drilling in hard and soft wood, plastics, acrylic and ceramic.

Also suitable for drilling hardened steel due to corrected cutting edge.

Technical description

Shank Ø	7 mm
Drill Ø	7 mm
Flute length	60 mm
overall length	100 mm
Tool material	Carbide
Standard	ISO 5468
Standard	DIN 8039
Use with impact / without impact	Impact drilling
Shank	Plain shank
Type of product	Masonry drill

