

**Garant**
**Carbide masonry drill set, Number of drills: 7**

**Order data**

Order number	786078 7
GTIN	4062406773496
Item class	71C

**Description**
**Version:**

Drill tipped with hard and tough carbide inserts and brazed at high temperature. Asymmetrical flute profile for good transport of drill dust.

**Hammer and rotary bits** with strong carbide cutter tip.

**Application:**

Primarily for **drilling dowel holes with hammer drills** in concrete, masonry, natural and synthetic stone.

Also for rotary drilling in hard and soft wood, plastics, acrylic and ceramic.

Also suitable for drilling hardened steel due to corrected cutting edge.

**Content:**

Drill No. 786070: 1 pc. each size 3; 4; 5; 6; 7; 8; 10

**Technical description**

Number of drills	7
Tool material	Carbide
Standard	ISO 5468
Standard	DIN 8039
Use with impact / without impact	Impact drilling

Shank	Plain shank
Type of product	Masonry drill

---

## Accessories

Carbide masonry drill Drill Ø 3 mm	786070 3
Carbide masonry drill Drill Ø 4 mm	786070 4
Carbide masonry drill Drill Ø 5 mm	786070 5
Carbide masonry drill Drill Ø 6 mm	786070 6
Carbide masonry drill Drill Ø 7 mm	786070 7
Carbide masonry drill Drill Ø 8 mm	786070 8
Carbide masonry drill Drill Ø 10 mm	786070 10