

**Garant**
**Carbide masonry drill, Drill Ø: 12mm**

**Order data**

Order number	786070 12
GTIN	4062406773465
Item class	71C

**Description**
**Version:**

Drill tipped with hard and tough carbide inserts and brazed at high temperature. Asymmetrical flute profile for good transport of drill dust.

**Hammer and rotary bits** with strong carbide cutter tip.

**Application:**

Primarily for **drilling dowel holes with hammer drills** in concrete, masonry, natural and synthetic stone.

Also for rotary drilling in hard and soft wood, plastics, acrylic and ceramic.

Also suitable for drilling hardened steel due to corrected cutting edge.

**Technical description**

Shank Ø	12 mm
Drill Ø	12 mm
overall length	150 mm
Flute length	85 mm
Tool material	Carbide
Standard	ISO 5468
Standard	DIN 8039
Use with impact / without impact	Impact drilling
Shank	Plain shank
Type of product	Masonry drill

