



Assembly tool set, 59 pieces in a tool rucksack, Number of pieces: 59



Order data

Order number	686016 59
GTIN	4062406773199
Item class	66H

Description

Version:

High-quality textile bags equipped with handy tool selections, as a companion for your day-to-day tasks.

Supplied with:

Heavy Duty Caliper: 1 pc. No. 410625 size 150

Tape measure: 1 pc. No. 462010 size 5

Double open ended spanner: 1 pc. each No. 610950 size 8×9; 10×11; 12×13; 16×17; 18×19

Hexagon key L-wrench set long with ball point: 1 pc. No. 627225 size 9 (1.5 – 10 mm)

Socket set 1/4 inch: 1 pc. No. 630368 size 6 (29 pieces)

Screwdriver for slot-head: 1 pc. each No. 660701 size 3, 4, 7

Screwdriver for Phillips: 1 pc. each No. 668401 size 0, 1, 2

Combination pliers: 1 pc. No. 702995 size 180

Water pump pliers: 1 pc. No. 706145 size 250

Snipe nose pliers, angled: 1 pc. No. 713595 size 200

Diagonal cutter: 1 pc. No. 725245 size 160

Engineer's hammer: 1 pc. No. 750125 size 300

Adjustable spanner: 1 pc. No. 813961 size 200

General-purpose knife: 1 pc. No. 845039 size 160

LED torch: 1 pc. No. 081437 size BLACK

Textile tool rucksack: 1 pc. No. 692267 size 1

Note:
Tool is supplied loose.

Technical description

Number of pieces	59
Square drive	1/4 in
Drive profile	Hexagon socket
Drive profile	Hexagon socket
Drive profile	Screwdriver for TORX® screws
Drive profile	Slot-head screwdriver
Type of product	Tool set

Accessories

General-purpose knife with zinc die-cast handle 18 mm overall length 160 mm	845039 160
Side cutter, bright finish, with grips overall length 160 mm	725245 160
Textile tool rucksack Type 1	692267 1
Screwdriver for slot-head, with power grip Blade width b 3 mm	660701 3
Snipe nose pliers, angled, bright finished, with grips Overall length 200 mm	713595 200
LED torch with batteries Colour BLACK	081437 BLACK
Double open ended spanner Jaw widths 18X19 mm	610950 18X19
Hexagon key L-wrench set nickel-plated Number of screwdrivers 9	627225 9
Screwdriver for slot-head, with power grip Blade width b 7 mm	660701 7
Vernier caliper with spring-loaded thumb-lock Measuring range 150 mm	410625 150
Socket set 1/4 inch square drive 29 pieces Type 6	630368 6

Tape measure Band length 5 m	462010 5
Screwdriver for Phillips, with power grip Cross-head size 1	668401 1
Screwdriver for Phillips, with power grip Cross-head size 2	668401 2
Double open ended spanner Jaw widths 8X9 mm	610950 8X9
Water pump pliers chemically blacked, with coated grips Overall length 250 mm	706145 250
Double open ended spanner Jaw widths 16X17 mm	610950 16X17
Screwdriver for Phillips, with power grip Cross-head size 0	668401 0
Double open ended spanner Jaw widths 10X11 mm	610950 10X11
Double open ended spanner Jaw widths 12X13 mm	610950 12X13
Vanadium combination pliers, bright finished, with two- part grips Overall length 180 mm	702995 180
Screwdriver for slot-head, with power grip Blade width b 4 mm	660701 4
Engineer's hammer Weight without handle 300 g	750125 300
Adjustable spanner with coated handle overall length 200 mm	813961 200