

Garant
GARANT Master Mute boring bar shank vibration damping, 15×D, System / shank Ø: QC/20

Order data

Order number	264898 QC/20
GTIN	4062406770204
Item class	29E

Description
Version:

Shank carbide reinforced.

Supplied with:

Reducing adaptor for coolant connection.

Note:

Do not clamp on the area marked S!

$D_{min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset } L_3.$

Convenient boring bar orientation by set-up head No. 265001.

Through-coolant: yes

System: QC

Overall length L: 340 mm

non-clamping range S: 118 mm

recommended clamping length: 80 mm

Assembly bolt set: 269026 1

Technical description

Plug connector for coolant connection	269208
System	QC
High-pressure connecting hose	269207
non-clamping range S	118 mm
recommended clamping length	80 mm
Assembly bolt set	269026 1

Overall length L	340 mm
Series	Master Mute
Boring depth up to	15×D
Vibration	damped
Through-coolant	yes
Type of product	Boring bar shanks