

**Garant**
**GARANT Master Mute boring bar shank vibration damping, 15×D, System / shank Ø: QC/32**

**Order data**

Order number	264898 QC/32
GTIN	4062406773625
Item class	29E

**Description**
**Version:**

Shank carbide reinforced.

**Supplied with:**

Reducing adaptor for coolant connection.

**Note:**

Do not clamp on the area marked S!

$D_{min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset } L_3.$

Convenient boring bar orientation by set-up head No. 265001.

Through-coolant: yes

System: QC

Overall length L: 544 mm

Centre offset H base body: 6 mm

non-clamping range S: 179 mm

recommended clamping length: 128 mm

Assembly bolt set: 269026 1

**Technical description**

Centre offset H base body	6 mm
Assembly bolt set	269026 1
non-clamping range S	179 mm
High-pressure connecting hose	269207
Plug connector for coolant connection	269208
System	QC

recommended clamping length	128 mm
Overall length L	544 mm
Series	Master Mute
Boring depth up to	15×D
Vibration	damped
Through-coolant	yes
Type of product	Boring bar shanks