

Garant GRIDLINE

ESD drawer, 12×20G, Drawer front height: 100mm**Order data**

Order number	972035 100
GTIN	4062406769789
Item class	9GG

Description**Version:**

100% full extension drawers in sturdy steel construction, with differential runners and 75 kg load capacity. Aluminium handles. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

Suitable for:

All ESD casings 16G.

Colour:

Drawer body and front light grey similar to RAL 7035 **ESD powder-coated**.

Technical description

Front height	100 mm
Usable depth in G	20
Usable width in G	12
Drawer/pull-out shelf load capacity	75 kg
Drawer usable area in G	12×20
Usable height	75 mm
Usable depth	500 mm
Usable width	300 mm
with individual drawer release system	no

Drawer runner extension (partial/full extension)	100 %
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	12×20G
Type of product	Drawer