

Garant GRIDLINE

ESD drawer, 12×20G, Drawer front height: 150mm**Order data**

| | |
|--------------|---------------|
| Order number | 972035 150 |
| GTIN | 4062406769802 |
| Item class | 9GG |

Description**Version:**

100% full extension drawers in sturdy steel construction, with differential runners and 75 kg load capacity. Aluminium handles. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

Suitable for:

All ESD casings 16G.

Colour:

Drawer body and front light grey similar to RAL 7035 **ESD powder-coated**.

Technical description

| | |
|-------------------------------------|--------|
| Front height | 150 mm |
| Usable width in G | 12 |
| Usable height | 125 mm |
| Drawer usable area in G | 12×20 |
| Usable depth in G | 20 |
| Drawer/pull-out shelf load capacity | 75 kg |
| Usable width | 300 mm |
| Usable depth | 500 mm |

| | |
|--|---------|
| with individual drawer release system | no |
| Drawer runner extension (partial/full extension) | 100 % |
| electrostatic characteristic | EGB/ESD |
| Drawer usable width × usable depth in G | 12×20G |
| Type of product | Drawer |