

Garant GRIDLINE

ESD casing 16G for individual configuration with drawers, 12×20G, Height of the housing: 400mm**Order data**

Order number	972030 400
GTIN	4062406769734
Item class	9GG

Description**Version:**

Drawer cabinet with sturdy steel construction. **For 100% full extension drawers** with differential runners and 75 kg load capacity. Can be locked centrally with a cylinder lock.

Application:

Drawer casing for individual fitting to the workstation No. 972010 – 972015 or to ESD workbenches No. 972150 – 972185.

Colour:

Body light grey similar to RAL 7035 **ESD powder-coated**.

Note:

All plastic components (e.g. covering caps) and handles are not ESD conductive. When equipping the casing with drawers, check that the sum of the individual drawer front heights adds up to the usable casing height.

Technical description

Weight	11.5 kg
Width in G	12

Usable height	325 mm
Depth	650 mm
Electronic locking system can be retrofitted	yes
Height	400 mm
Version	for individual configuration
Width	400 mm
Depth in G	20
Drawer usable area in G	12×20
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	12×20G
Type of product	Tool cabinet body