

Garant GRIDLINE

**ESD drawer with one-handed individual drawer release system, 12×20G,
Drawer front height: 100mm****Order data**

Order number	972036 100
GTIN	4062406773847
Item class	9GG

Description**Version:**

100% full extension drawers in sturdy steel construction, with differential runners and 75 kg load capacity. Aluminium handles. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **one-handed individual drawer release system** prevents the opening of drawers during transport. Essential for all roller cabinets and mobile workbenches and cabinet casings.

Suitable for:

All ESD casings 16G.

Colour:

Drawer body and front light grey similar to RAL 7035 **ESD powder-coated**.

Technical description

Drawer/pull-out shelf load capacity	75 kg
Usable depth in G	20
Front height	100 mm
Usable width in G	12
Usable height	75 mm
Individual drawer release system	One-hand
Drawer usable area in G	12×20

Usable depth	500 mm
Usable width	300 mm
with individual drawer release system	yes
Drawer runner extension (partial/full extension)	100 %
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	12×20G
Type of product	Drawer