

Garant GRIDLINE

**ESD casing 16G for individual configuration with drawers, 12×20G, Height of the housing: 500mm****Order data**

Order number	972030 500
GTIN	4062406769741
Item class	9GG

**Description****Version:**

Drawer cabinet with sturdy steel construction. **For 100% full extension drawers** with differential runners and 75 kg load capacity. Can be locked centrally with a cylinder lock.

**Application:**

Drawer casing for individual fitting to the workstation No. 972010 – 972015 or to ESD workbenches No. 972150 – 972185.

**Colour:**

Body light grey similar to RAL 7035 **ESD powder-coated**.

**Note:**

All plastic components (e.g. covering caps) and handles are not ESD conductive. When equipping the casing with drawers, check that the sum of the individual drawer front heights adds up to the usable casing height.

**Technical description**

Depth in G	20
Width in G	12

Height	500 mm
Version	for individual configuration
Usable height	425 mm
Weight	13 kg
Depth	650 mm
Width	400 mm
Electronic locking system can be retrofitted	yes
Drawer usable area in G	12x20
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	12x20G
Type of product	Tool cabinet body