

Garant GRIDLINE

ESD casing 16G for individual configuration with drawers, 12×20G, Height of the housing: 300mm



Order data

Order number	972030 300
GTIN	4062406769727
Item class	9GG

Description

Version:

Drawer cabinet with sturdy steel construction. **For 100% full extension drawers** with differential runners and 75 kg load capacity. Can be locked centrally with a cylinder lock.

Application:

Drawer casing for individual fitting to the workstation No. 972010 – 972015 or to ESD workbenches No. 972150 – 972185.

Colour:

Body light grey similar to RAL 7035 **ESD powder-coated**.

Note:

All plastic components (e.g. covering caps) and handles are not ESD conductive. When equipping the casing with drawers, check that the sum of the individual drawer front heights adds up to the usable casing height.

Technical description

Version	for individual configuration
Usable height	225 mm
Electronic locking system can be retrofitted	yes

Weight	9.5 kg
Depth in G	20
Height	300 mm
Width	400 mm
Width in G	12
Depth	650 mm
Drawer usable area in G	12×20
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	12×20G
Type of product	Tool cabinet body