

Garant GRIDLINE

**ESD drawer, 12×20G, Drawer front height: 200mm****Order data**

Order number	972035 200
GTIN	4062406773816
Item class	9GG

**Description****Version:**

100% full extension drawers in sturdy steel construction, with differential runners and 75 kg load capacity. Aluminium handles. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

**Suitable for:**

All ESD casings 16G.

**Colour:**

Drawer body and front light grey similar to RAL 7035 **ESD powder-coated**.

**Technical description**

Drawer/pull-out shelf load capacity	75 kg
Usable depth in G	20
Front height	200 mm
Usable width in G	12
Usable height	175 mm
Drawer usable area in G	12×20
Usable depth	500 mm
Usable width	300 mm

with individual drawer release system	no
Drawer runner extension (partial/full extension)	100 %
electrostatic characteristic	EGB/ESD
Drawer usable width × usable depth in G	12×20G
Type of product	Drawer