

# AEG

## Impact wrench, Type: BSS18MTF12



### Order data

Order number	074016 BSS18MTF12
GTIN	4058546374570
Item class	07A

### Description

#### Version:

Powerful 18 V cordless impact wrench with 1/2 inch square arbor.

- **LED illumination of the working area.**
- **Handle with soft-grip coating.**
- **Belt hook.**
- **Torque adjustment in 4 stages including auto-stop for optimum tightening and releasing of wheel nuts.**
- **brushless motor.**

#### Supplied with:

Without battery and without charger, in a cardboard box.

#### Note:

For suitable spare battery see No. 073846 – 073848. See No. 073844 for battery starter sets.

### Technical description

Tool arbor drive profile	External square drive
Number of rechargeable batteries contained	0

Power supply	Rechargeable battery-powered
maximum torque	785 Nm
Number of impacts	0 - 3800 min <sup>-1</sup>
Battery voltage	18 V
Manufacturer's designation	BSS18MTF12
maximum screw Ø (8.8 - 12.9)	M16
Type of rechargeable battery	Lithium-ion
typical application	Heavy Duty
Tool arbor size	1/2 in
Weight	1.65 kg
suitable battery - supplier / battery type / voltage	AEG type AS 18 V
Type of product	Impact wrench