

AEG

Angle grinder Cordless, Type: BEWS18BLPX



Order data

| | |
|--------------|-------------------|
| Order number | 077125 BEWS18BLPX |
| GTIN | 4058546223649 |
| Item class | 07A |

Description

Version:

Brushless high-performance 18 V angle grinder in a compact design.

- **Quick guard adjustment**
- **LED warning lamp for protection against overloading**
- **Flat and sturdy metal gearbox casing for working in hard-to-reach spots**

Supplied with:

Without battery and without charger, in a cardboard box.

Note:

For suitable replacement batteries see No. 073846-073848. See No. 073844 for battery starter sets.

suitable battery - supplier / battery type / voltage: AEG type AS 18 V

Manufacturer's designation: BEWS18-125BLPX

Battery voltage: 18 V

maximum speed: 11000 min⁻¹

maximum disc Ø: 125 mm

maximum cutting depth: 22 mm

Weight: 2.3 kg

Technical description

| | |
|--|------------------------------|
| maximum cutting depth | 22 mm |
| Manufacturer's designation | BEWS18-125BLPX |
| Kick-back stop | no |
| Soft start | no |
| Battery voltage | 18 V |
| Dead man's circuit | yes |
| Restart block | yes |
| maximum disc Ø | 125 mm |
| Weight | 2.3 kg |
| suitable battery - supplier / battery type / voltage | AEG type AS 18 V |
| Power supply | Rechargeable battery-powered |
| Overload protection | yes |
| maximum speed | 11000 min ⁻¹ |
| Type of product | Angle grinder |