

**Pair of cut-resistant heat resistant gloves, Glove size: 9****Order data**

Order number	094619 9
GTIN	4062406773380
Item class	02H

Description**Version:**

HOLEX cut-resistant, heat-protection gloves in 10-gauge knitting technology. Cut protection class C. Contact heat protection up to 250°C (maximum 15 seconds).

Standard:

EN 388; EN 407; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

EN 388	4X31C
EN 407	X2XXXX
Contact heat up to	250 °C
Backing material	Polyester, aramid, glass fibre
Coating	Nitrile
Colour	orange / black

Application	reusable
Application range	All-round
Knitted technology	10G
Cut protection class	C
Standard	EN 407
Type of product	Heat protection gloves