

Garant**HCT digital caliper IP67 with Bluetooth, Measuring range: 150mm****Order data**

Order number	412781 150
GTIN	4062406773922
Item class	41A

Description**Version:**

IP 67 HCT digital caliper with **Bluetooth 5.0. Easy-to-read, high-contrast LCD display with 11.5 mm character height.** Very long battery running time due to modern energy-efficient measurement system. The system switches automatically into power-saving mode after 10 minutes; moving the caliper reactivates it. There is no loss of the measurement value or zero point. 2-component body with **non-slip Haptoprene surface.** The caliper is resistant to water, coolant, oil, and dust. The measuring faces are precision-lapped. Compatible with the optional HCT (Hoffmann Group Connected Tools) mobile app. Available free of charge for Android and iOS. Can also be used via a Human Interface Device (HID).

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032.

Spare part:

Battery holder No. 412237 size B.

Technical description

Depth gauge	rectangular 3.7×1.3
Calibration	A1
Reversible reading	mm / inch
Number of batteries contained	1
Standard	ISO 13385

International size	CR2032
Article no of the battery / rechargeable battery fitted	081560
IP Index of Protection	IP 67
Series	HCT
Scale divisions	0.0005 in
Power supply	Battery-powered
Battery type	Button cell
Jaw length	40 mm
Wireless application	HID (Human Interface Device)
Wireless application	HCT Mobile App
Wireless application	HCT Windows app
Scale divisions	0.01 mm
Depth gauge available	yes
Measurement deviation E MPE	± 0.02 mm
Interface	Bluetooth interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------

Cover for digital calipers Type B	412237 B
Screw for depth gauge holder	412236
Type SPRING	412240 SPRING