

**Garant****HCT digital caliper IP67 with Bluetooth, Measuring range: 200mm****Order data**

Order number	412781 200
GTIN	4062406773939
Item class	41A

**Description****Version:**

IP 67 HCT digital caliper with **Bluetooth 5.0. Easy-to-read, high-contrast LCD display with 11.5 mm character height.** Very long battery running time due to modern energy-efficient measurement system. The system switches automatically into power-saving mode after 10 minutes; moving the caliper reactivates it. There is no loss of the measurement value or zero point. 2-component body with **non-slip Haptoprene surface.** The caliper is resistant to water, coolant, oil, and dust. The measuring faces are precision-lapped. Compatible with the optional HCT (Hoffmann Group Connected Tools) mobile app. Available free of charge for Android and iOS. Can also be used via a Human Interface Device (HID).

**Function:**

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

1 battery No. 081560 size CR2032.

**Spare part:**

Battery holder No. 412237 size B.

**Technical description**

Reversible reading	mm / inch
Scale divisions	0.0005 in
Depth gauge available	yes
Calibration	A1
Depth gauge	rectangular 3.7×1.3

Jaw length	50 mm
International size	CR2032
Wireless application	HID (Human Interface Device)
Wireless application	HCT Mobile App
Wireless application	HCT Windows app
Scale divisions	0.01 mm
IP Index of Protection	IP 67
Standard	ISO 13385
Battery type	Button cell
Number of batteries contained	1
Power supply	Battery-powered
Article no of the battery / rechargeable battery fitted	081560
Series	HCT
Measurement deviation E MPE	± 0.03 mm
Interface	Bluetooth interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

## Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

## Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------

Cover for digital calipers Type B	412237 B
Screw for depth gauge holder	412236
Type SPRING	412240 SPRING