

**Garant****HCT digital caliper IP67 with Bluetooth, Measuring range: 300mm****Order data**

Order number	412781 300
GTIN	4062406773946
Item class	41A

**Description****Version:**

IP 67 HCT digital caliper with **Bluetooth 5.0. Easy-to-read, high-contrast LCD display with 11.5 mm character height.** Very long battery running time due to modern energy-efficient measurement system. The system switches automatically into power-saving mode after 10 minutes; moving the caliper reactivates it. There is no loss of the measurement value or zero point. 2-component body with **non-slip Haptoprene surface.** The caliper is resistant to water, coolant, oil, and dust. The measuring faces are precision-lapped. Compatible with the optional HCT (Hoffmann Group Connected Tools) mobile app. Available free of charge for Android and iOS. Can also be used via a Human Interface Device (HID), without depth gauge

**Function:**

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

1 battery No. 081560 size CR2032.

**Spare part:**

Battery holder No. 412237 size B.

**Technical description**

Scale divisions	0.01 mm
Battery type	Button cell
Power supply	Battery-powered
Number of batteries contained	1
International size	CR2032

Calibration	A1
Jaw length	64 mm
Reversible reading	mm / inch
Wireless application	HID (Human Interface Device)
Wireless application	HCT Mobile App
Wireless application	HCT Windows app
Article no of the battery / rechargeable battery fitted	081560
Scale divisions	0.0005 in
Depth gauge available	no
Series	HCT
Standard	ISO 13385
IP Index of Protection	IP 67
Measurement deviation E MPE	$\pm 0.03$ mm
Interface	Bluetooth interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

## Services

CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300
DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300

## Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Cover for digital calipers Type B	412237 B

Screw for depth gauge holder	412236
Type SPRING	412240 SPRING