

Garant
HCT digital depth gauge IP67 with Bluetooth, Measuring range: 200mm

Order data

Order number	418685 200
GTIN	4062406773977
Item class	41A

Description
Version:

Very large high-contrast LCD display with 11.5 mm character height. Very long battery running time due to modern energy-efficient measurement system. The system switches automatically into power-saving mode after 20 minutes; moving the caliper reactivates it. There is no loss of the measurement value or zero point. 2-component body with **non-slip Haptoprene surface**. The measuring faces are precision-lapped. Measuring beam has a slender hardened measuring pin at the front, \varnothing 1.5 mm, 5 mm long. With preset (dimension selection in advance).

IP67 HCT digital depth gauge with Bluetooth 5.0. **Very large high-contrast LCD display with 11.5 mm character height.** Very long battery running time due to modern energy-efficient measurement system. The system switches automatically into power-saving mode after 10 minutes; moving the caliper reactivates it. There is no loss of the measurement value or zero point. 2-component body with **non-slip Haptoprene surface**. The measuring faces are precision-lapped. Measuring beam has a slender hardened measuring pin at the front, \varnothing 1.5 mm, 5 mm long. With preset (dimension selection in advance).

Version **with Bluetooth**. Compatible with the optional HCT (Hoffmann Group Connected Tools) mobile app. Available free of charge for Android and iOS. Can also be used via a Human Interface Device (HID).

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032.

Optional extras:

Extension base 320 mm long No. 418689, measuring tip for caliper jaws No. 418630

Technical description

Reversible reading	0.0005 in
Series	HCT
Reversible reading	0.01 mm
IP Index of Protection	IP 67
Interface	Bluetooth interface
Number of batteries contained	1
Calibration	A1
Cross-section measuring beam	16x3.5 mm
Battery type	Button cell
Bridge length	100 mm
Power supply	Battery-powered
Article no of the battery / rechargeable battery fitted	081560 CR2032
Wireless application	HID (Human Interface Device)
Wireless application	HCT Mobile App
Wireless application	HCT Windows app
Measurement deviation E MPE	±0.03 mm
Standard	ISO 13385
Reversible reading	mm / inch
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Depth gauge

Services

Calibration Vernier hook depth gauge maximum measuring range 200 mm	021220 200
	021230 200

DAkKS calibration Vernier hook depth gauge maximum
measuring range 200 mm

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Cover for digital calipers Type B	412237 B
Screw for depth gauge holder	412236