



Self-levelling cross-hair laser LINO, Type: L6RS



Order data

Order number	468486 L6RS
GTIN	7640180530640
Item class	47C

Description

Version:

Robust, ergonomic plastic casing; proof against dust and splashed water. Self-levelling multi-mains laser with 3× 360° laser lines. One horizontal and two vertical 360° laser lines. Laser lines thin, sharp and clearly visible. Laser power can be set in 3 stages for better visibility or longer operating time. Self-levelling over long distances in the event of inclined positions. Time saving by easy setting up of the zero point. Fixed zero point thanks to integral base. Simple and precise alignment of the laser lines by $\pm 10^\circ$. Memory function of personal settings. Dust-proof and splash-proof. The triple power-supply concept permits uninterrupted work. Can optionally be operated with Li-ion battery, AA batteries or power supply unit.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

3× battery No. 081561 LR6, laser target plate, bag.

Technical description

Height	110 mm
--------	--------

Weight	530 g
Threaded socket for stand	1/4 UNC in
Number of batteries contained	3
Colour of the laser	red
Range with receiver	70 m
Article no of the battery / rechargeable battery fitted	081561 LR6
Range	25 m
IP Index of Protection	IP 54
Width	60 mm
Power supply	Battery-powered
Error limit	± 0.2 mm/m
Levelling range	± 4 degrees
Depth	100 mm
Series	LINO
Diameter with receiver	140 m
Working time	25 h
Type of product	Cross laser

Accessories

Alkaline-manganese batteries International size LR6	081561 LR6
---	------------