

STARCKE®**Paper velour-backed abrasive triangle (A) 6 holes, Grit: 120****Order data**

Order number	557636 120
GTIN	4002748777769
Item class	56Z

Description**Version:**

Starcke sanding paper 540 FK (F paper) with **high strength and dense distribution**. High material removal rates due to specially treated aluminium oxide (**A**).

Application:

General purpose for grinding metal, non-ferrous metals, varnish, paint, wood, and plastic.

Suitable for:

Suitable for Bosch Multi-Cutter.

Technical description

Grit	120
Grit designation	medium
Grinding media	Aluminium oxide
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
Width	88 mm
Length	93 mm
Type of product	Hook-and-loop sandpaper

User data

	Suitability	V_c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable		
Uni	suitable		
dry	suitable		