

**STARCKE®****Paper velour-backed abrasive triangle (A) 6 holes, Grit: 80****Order data**

Order number	557636 80
GTIN	4002748777752
Item class	56Z

**Description****Version:**

Starcke sanding paper 540 FK (F paper) with **high strength and dense distribution**. High material removal rates due to specially treated aluminium oxide (**A**).

**Application:**

**General purpose** for grinding metal, non-ferrous metals, varnish, paint, wood, and plastic.

**Suitable for:**

Suitable for Bosch Multi-Cutter.

**Technical description**

Grit designation	coarse
Grit	80
Grinding media	Aluminium oxide
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
Width	88 mm
Length	93 mm
Type of product	Hook-and-loop sandpaper

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable		
Uni	suitable		
dry	suitable		