



DFG manual force gauge, Measuring range: 250N



Order data

Order number	479025 250
GTIN	2050002070752
Item class	47F

Description

Version:

Universal force gauge with colour display for precisely measuring tensile and compressive forces. Sturdy die-cast housing.

- **Displays the current force value and peak value.**
- **Programmable function keys.**
- **Monitoring of tolerance limits with visual and acoustic display.**
- **Memory for storing measurements.**
- **Statistical evaluation of saved values.**
- **Interface for exporting data.**
- **Display can be switched between N, gf, kgf, lbf, ozf.**

Supplied with:

Carrying case, charging plug with USB connecting cable, accessories (pressure pad, hook, tip, fin, V-slot, extension).

Optional extras:

Manual test stands No. 479029.

Technical description

Measured value memory	50
-----------------------	----

Measuring range	0 - 250 N
Power supply	Rechargeable battery-powered
Resolution	0.05 N
Length	191 mm
Accuracy	0.2
Height	42 mm
Width	84 mm
Interface	Digimatic interface
Interface	USB interface
Measurement technology	digital
Type of product	Draw bar pulling force gauge