



DFC manual force gauge, Measuring range: 250N



Order data

Order number	479027 250
GTIN	2050002071537
Item class	47F

Description

Version:

Universal force gauge with colour display for precisely measuring tensile and compressive forces. Sturdy die-cast housing.

- **Displays the current force value and peak value.**
- **Programmable function keys.**
- **Monitoring of tolerance limits with visual and acoustic display.**
- **Memory for storing measurements.**
- **Statistical evaluation of saved values.**
- **Interface for exporting data.**
- **Display can be switched between N, gf, kgf, lbf, ozf.**
- **Measured values can be transmitted via Bluetooth.**
- **Average force over time.**

Supplied with:

Carrying case, charging plug with USB connecting cable, accessories (pressure pad, hook, tip, fin, V-slot, extension).

Optional extras:

Manual test stands No. 479029.

Technical description

Length	191 mm
Resolution	0.025 N
Height	42 mm
Accuracy	0.1
Power supply	Rechargeable battery-powered
Width	84 mm
Wireless application	HID (Human Interface Device)
Measured value memory	99
Measuring range	0 - 250 N
Interface	USB interface
Interface	Digimatic interface
Interface	Bluetooth interface
Measurement technology	digital
Type of product	Draw bar pulling force gauge