

BENNING**Socket tester, Type: SDT1****Order data**

Order number	473275 SDT1
GTIN	4014651200531
Item class	47A

Description**Version:**

Quick and easy check of earthed plug sockets for correct connection. Wiring errors such as missing PE, N and L lines as well as mixing up of L and PE lines are clearly displayed via 3 LEDs. Easily understandable status table gives information about the correct connection (OK, green) and the type of error (red) of the earthed plug socket.

- **Active PE test with contact electrode and LC display warns about the presence of a dangerous touch voltage (>50 V) at the earth conductor connection (PE).**
- **Test button for triggering 30 mA FI/RCD earth leak trip switches.**
- **Clear display via LEDs and LC display.**

Application:

Socket test, 30 mA test FI/RCD earth leak trip switches.

Technical description

Manufacturer's designation	SDT 1
Power supply	Mains-powered
Weight	70 g
Plug version	SCHUKO® socket

Plug type	F
Width	72 mm
Length	78 mm
Depth	80 mm
Type of product	Continuity and semiconductor tester