



simturn AX boring-out insert, right-hand CBN, L₂ = 6.1 mm, Ø D_{min}: 1,4mm



Order data

Order number	270577 1,4
GTIN	2050002065871
Item class	24V

Description

Version:

Tool material: CBN8

Technical description

f	0.6 mm
maximum cutting depth a _{p max}	0.07 mm
Ø D	4 mm
for bores from Ø D _{min}	1.4 mm
Radius R	0.1 mm
Through-coolant	no
Manufacturer's designation	A53ZCBN8
Usable length	6.1 mm
Product name attribute	L ₂ = 6.1 mm
Type of product	Cutter insert for turning

User data

	Suitability	V _c	ISO code
Steel < 67 HRC	suitable		

continuous	suitable
dry	suitable