



simturn AX boring-out insert, right-hand CBN, L₂ = 20.3 mm, Ø D_{min}: 5,2mm



Order data

Order number	270583 5,2
GTIN	2050002066007
Item class	24V

Description

Version:

Tool material: CBN8

Technical description

f	2.45 mm
Through-coolant	no
Ø D	5 mm
for bores from Ø D _{min}	5.2 mm
maximum cutting depth a _{p,max}	0.26 mm
Radius R	0.2 mm
Manufacturer's designation	AHAXCBN8
Usable length	20.3 mm
Product name attribute	L ₂ = 20.3 mm
Type of product	Cutter insert for turning

User data

	Suitability	V _c	ISO code
Steel < 67 HRC	suitable		

continuous	suitable
dry	suitable